

Product Overview

AC13051015A


Solid State Replacement for Clairex Photomods Neon Modules CLM3120 and CLM4120

This solid state circuitry PCB is provided as a replacement module for the obsolete Clairex CLM lamp modules. Customization is available upon request.


Duplicating the CML lamp, the solid state PCB accepts 120VAC input and converts to a transistor output using a high voltage optocoupler. Resistance is provided to scale the AC input signal as well as an AC load resistor to provide similar AC current load to the original circuit.



Clairex Neon Lamp Module



Solid State Replacement Module



Model: AC13051015A




Technical Data:

Pin Spacing	.30" x 2.8"
Pin Diameter	.025"
Max Input Current	+/-60mA
Max Collector-	70V
Emitter Voltage	
Max Collector	50mA
Current	


Please contact the factory for additional technical information and schematic.

sales@advantagecircuits.com

Pricing: 1-10 units = \$40 each.



CLM3120A



Clairex Neon Lamp Module Datasheet (1 of 2):



CLAIREX ELECTRONICS DIV

■ 2142799 0000802 b 19E D

T-41.81

Photomods®

CLM4120A Neon Modules


- Long Life
- Fast Rise and Decay
- Low Impedance
- Complete Electrical and Mechanical Isolation
- High Cell To Lamp Voltage Breakdown

APPLICATIONS


CLM3120A and CLM4120A — Neon lamp modules can provide electrically isolated (signal) coupling between power-line or other high voltage (AC or DC) circuitry and low voltage (solid state) process control, or indicating (alarm)

Remote indication or control is facilitated since the output is electrically isolated and wiring need not conform to powerline code requirements.

rne neon lamp may serve as a (circuit) component in the high voltage circuitry. In suitable circuit configurations, the cell will serve to monitor voltage, resistance or capacitance in addition to the simple indication of power ON or OFF. The neon lamp may serve as a (circuit) component in the



Voltage (presence) Indicator



 $= \frac{V-70}{1.7}$ With V, R_{CELL} will be low Without V, R CELL will be very high (V: RMS or DC)

OUTPUT RESISTANCE

TECHNICAL DATA


	AC LAMP	AC LAMP OPERATION		DC LAMP OPERATION ①			
MODULE PART NUMBER	Rated Lamp Voltage 60 Hz V _R Volts	Output ① Resistance @ Rated Voltage R _{CA} Ohms	Control Lamp Current I _R Milliamps	Control Lamp Life Hours	Output Resistance At I _R R _{CD} Ohms	Minimum Off Resistance R _D Megohms	
İ		Maximum ②		Minimum	Maximum	<u> </u>	
			2	2000 ①	750	100	
CLM 3120A 120	1150	1	50,000 ③	1200	10 Seconds after Lamp Turn off.		
			2	2,000 ①	135	1	
CLM 4120A	120	160	1	50,000 ③	200	10 Seconds after Lamp Turn Off.	

---8-13---

Advantage Circuits, Ltd. 3512 Industry Rd. Rootstown, Ohio 44272 sales@advantagecircuits.com

Copyright ©Advantage Circuits, Ltd. 2006. 330-256-7768 RevA

www.advantagecircuits.com



Clairex Neon Lamp Module Datasheet (2 of 2):

CLAIREX ELECTRONICS DIV

19E D == 2142799 0000803 8 ==

T-41-81

Photomods® **Neon Modules**

SPEED OF RESPONSE

	AFTER LAMP HAS BEEN ON FOR 24 HOURS				NO LAMP POWER FOR 96 HOURS PRIOR TO MEASUREMENT			
MODULE PART NUMBER	T Time To: Time To:		m Decay G Maximum			Maximum Decay O Time To:		
		2 X R _{2.5} O Milliseconds	30 X R _{2.5} [©] Milliseconds	5 X R _{2.5} © Milliseconds	5 X R _{2.5} © Milliseconds	2 X R _{2.5} Ø Milliseconds	30 X R _{2.5} [©] Milliseconds	5 X R _{2.5} O Milliseconds
CLM3120A	0.6	1.6	50	12	5.0	7.0	60	18
CLM4120A	2.5	5.0	125	30	5.0	8.0	250	55

MAXIMUM RATINGS	VOLTAGE ACROSS CELL 200V - PEAK AC
	MAXIMUM POWER

NOTES ON DATA

- ① Data is taken using a 27K resistor in series with the neon lamp. Note: SERIES RESISTOR IS NOT INCLUDED IN THE MODULE.
- 2 Values are taken after lamp power has been applied for more than 24 hours.
- 3 Lamp currents below 1 milliamp are not recommended.
- 4 High-brightness lamp rating: for 10 volt change in breakdown or maintaining voltage. Breakdown voltage: 75-135 volts; Maintaining voltage; approximately 70 volts.
- 5 Calculated operating time for 10 volt change in breakdown or maintaining voltage.

- 6 After five (or more) seconds illumination at 2 milliamps measured with 30V applied to cell.
- \bigcirc Maximum rise time is the time from application of lamp voltage to the stated multiple of the resistance at 2.5 milliamps on the neon $(R_{2.0})$.
- $\fbox{8}$ Maximum decay time is the time from lamp turn off to the stated multiple of the resistance at $(R_{2.5})$.
- \P $R_{2.5}$ is the cell resistance with 2.5 milliamps on the neon lamp. Rise time is given for multiples of 5 and 2 times the resistance at 2.5 milliamps. Decay time is given for multiples of 30 and 5.
- 10 Derated linearly to zero at 75°C as measured on the cell.

---8-14---